



TYPICAL SETUP



VIEW "A-A"
SCALE 2:1




⑥ MAX. OPENING OF DOOR
90 DEGREE


NOTE:

- ① INTERMEDIATE CYLINDER IS CUSTOM MADE AS FLOOR THICKNESS MAY VARY FROM HOME TO HOME.
- ② INTERMEDIATE CYLINDER IS CUSTOM MADE AS ROOM HEIGHT MAY VARY FROM HOME TO HOME.
- ③ MINIMUM ALLOWABLE HEIGHT IS 2340 mm
- ④ MINIMUM ALLOWABLE HEIGHT AS SHOWN FOR THIS TAPE OF INSTALLATION.
- ⑤ INTERNAL DIAMETER OF CABIN WITHOUT THE COLUMNS IS 640 mm AND THE INTERNAL CABIN HEIGHT IS 2007 mm
- ⑥ DOOR WIDTH IS 508 mm
- ⑦ MAX. ELEVATOR HEIGHT IS 10m.

OPTION: REMOTE LOCATION OF HEAD UNIT



DETAIL "A"
(TYPICAL OF FLOOR PENETRATION)



Information contain herein is the property of Pneumatic Vacuum Elevators LLC. No reproduction or disclosure of this information may be made by the recipient to any person or organization without the written consent of Pneumatic Vacuum Elevators LLC.



TYPICAL PVE30 HOME INSTALLATION
FOR A 4STOP ELEVATOR

Designed by	Scale	Drawing No.	Rev	Date
HS	1:1	D-30-3CYL4	0	04/10/12